



Slotted pan head screw DIN 85 Stainless steel A2 70 M8X60

Article number	51140.080.060
Brand	-
UBB	951353081122
UNSPSC	31161504
EAN	8715492273642
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M8
Length	60 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	85
BS	≈4183
ISO	≈1580
ASME	≈B18.6.7M
NEN	≈1603
NF	≈E25-128

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	16
Full thread if $L \leq$	40
k (max.)	4.8
L (mm)	60
n	2
P	1.25
t (min.)	1.9

Technical Drawing

