



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M2,5X3

Article number	51230.025.003
Brand	-
UBB	500633192926
UNSPSC	31161518
EAN	8715494613521
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2.5
Length	3 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

NEN	2344
NF	E27-182
ISO	4028
ASME	B18.3.6M
BS	4168-4
DIN	915

Technical Specification

d-D	M2.5
dp (max.)	1.5
L (mm)	3
P	0.45
s	1.3
t (min.)	1.2
z long (min.)	1.25
z long if L ≥	5
z short (min.)	0.63

Technical Drawing

