

Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M4X12



Article number	51230.040.012
Brand	-
UBB	500633193346
UNSPSC	31161518
EAN	8715494613569
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M4
Length (L) (mm)	12
Material	Stainless steel
Driving features	Hexagon socket
Thread direction	Right
Thread	Metric thread
Material technical	A2

Info These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

NF	E27-182
BS	4168-4
ASME	B18.3.6M
ISO	4028
DIN	915

Technical Specification

d_p (max.)	2.5
P	0.70
s	2
t (min.)	1.5
z long (min.)	2
z long if $L \geq$	8
z short (min.)	1

Technical Drawing

