



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M2,5X6

Article number	51300.025.006
Brand	-
UBB	950353275767
UNSPSC	31161504
EAN	8715492281104
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M2.5
Length	6 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7046-1
NF	≈E25-119-1
DIN	965

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
Full thread if L ≤	20
k (max.)	1.5
L (mm)	6
No. cross recess	1
P	0.45

Technical Drawing

