



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M3X6

Article number	51300.030.006
Brand	-
UBB	950353276344
UNSPSC	31161504
EAN	8715492281173
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	6 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	6
No. cross recess	1
P	0.5

Technical Drawing

