



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M3X8

Article number	51300.030.008
Brand	-
UBB	950353536630
UNSPSC	31161504
EAN	8715492281197
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	8
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	7046-2-H
NF	E25-119-2
DIN	965 A-H

Technical Specification

Thread length (min.)	19
d_k (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
No. cross recess	1
P	0.50

Technical Drawing

