



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M4X35

Article number	51300.040.035
Brand	-
UBB	951353580180
UNSPSC	31161504
EAN	8715492281388
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	35 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	35
No. cross recess	2
P	0.7

Technical Drawing

