



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M5X12

Article number	51300.050.012
Brand	-
UBB	950353277748
UNSPSC	31161504
EAN	8715492281456
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	12 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	965
NF	≈E25-119-1
ISO	≈7046-1

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	12
No. cross recess	2
P	0.8

Technical Drawing

