



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M5X50

Article number	51300.050.050
Brand	-
UBB	950353551712
UNSPSC	31161504
EAN	8715492281531
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	50 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	965
ISO	≈7046-1
NF	≈E25-119-1

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	50
No. cross recess	2
P	0.8

Technical Drawing

