



## Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M6X35

|                |               |
|----------------|---------------|
| Article number | 51300.060.035 |
| Brand          | -             |
| UBB            | 950353278993  |
| UNSPSC         | 31161504      |
| EAN            | 8715492281647 |
| PKG. of 100    | Full Box Only |

### Technical Parameters

|                    |                  |
|--------------------|------------------|
| Diameter           | M6               |
| Length             | 35 mm            |
| Class              | 70               |
| Driving features   | Phillips         |
| Head shape         | Countersunk head |
| Material           | Stainless steel  |
| Material technical | A2               |
| Thread             | Metric thread    |

### Standards

|     |            |
|-----|------------|
| DIN | 965        |
| NF  | ≈E25-119-1 |
| ISO | ≈7046-1    |

### Technical Specification

|                         |    |
|-------------------------|----|
| d-D                     | M6 |
| Thread length (min.)    | 28 |
| dk (max.)               | 11 |
| Full thread if $L \leq$ | 35 |
| k (max.)                | 3  |
| L (mm)                  | 35 |
| No. cross recess        | 3  |
| P                       | 1  |

### Technical Drawing

