



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M6X55

Article number	51300.060.055
Brand	-
UBB	500571332203
UNSPSC	31161504
EAN	8715494115612
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	55 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7046-1
DIN	965
NF	≈E25-119-1

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	55
No. cross recess	3
P	1

Technical Drawing

