



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M6X75

Article number	51300.060.075
Brand	-
UBB	500571332385
UNSPSC	31161504
EAN	8715494115629
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	75 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
DIN	965
ISO	≈7046-1

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if L ≤	35
k (max.)	3
L (mm)	75
No. cross recess	3
P	1

Technical Drawing

