



Cross recessed countersunk head screw Phillips DIN 965 Stainless steel A2 70 M10X40

Article number	51300.100.040
Brand	-
UBB	500502343063
UNSPSC	31161504
EAN	8715494079686
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	40 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7046-1
DIN	965
NF	≈E25-119-1

Technical Specification

d-D	M10
Thread length (min.)	40
dk (max.)	18
Full thread if $L \leq$	50
k (max.)	5
L (mm)	40
No. cross recess	4
P	1.5

Technical Drawing

