



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M2X4

Article number	51302.020.004
Brand	-
UBB	951353117108
UNSPSC	31161504
EAN	8715492281913
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M2
Length	4 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
DIN	965
ISO	≈7046-1

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	4
No. cross recess	1
P	0.4

Technical Drawing

