



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M2,5X6

Article number	51302.025.006
Brand	-
UBB	951353118197
UNSPSC	31161504
EAN	8715492282026
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M2.5
Length	6 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	965
NF	≈E25-119-1
ISO	≈7046-1

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
Full thread if L ≤	20
k (max.)	1.5
L (mm)	6
No. cross recess	1
P	0.45

Technical Drawing

