



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Stainless steel A2 M2X3

Article number	51320.020.003
Brand	-
UBB	500571409852
UNSPSC	31161504
EAN	8715494121248
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	3 mm
Class	70
Driving features	Phillips
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-120
DIN	966
ISO	≈7047

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
f ≈	0.5
Full thread if L ≤	18
k (max.)	1.2
L (mm)	3
No. cross recess	1
P	0.4

Technical Drawing

