



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Stainless steel A2 M2X5

Article number	51320.020.005
Brand	-
UBB	500571410090
UNSPSC	31161504
EAN	8715494121262
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	5 mm
Class	70
Driving features	Phillips
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7047
DIN	966
NF	≈E25-120

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
f ≈	0.5
Full thread if L ≤	18
k (max.)	1.2
L (mm)	5
No. cross recess	1
P	0.4

Technical Drawing

