



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Stainless steel A2 M2X16

Article number	51320.020.016
Brand	-
UBB	500571410587
UNSPSC	31161504
EAN	8715494121316
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	16 mm
Class	70
Driving features	Phillips
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	966
NF	≈E25-120
ISO	≈7047

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
f ≈	0.5
Full thread if L ≤	18
k (max.)	1.2
L (mm)	16
No. cross recess	1
P	0.4

Technical Drawing

