

Cross recessed raised cheese head screw Phillips DIN 7985-H Stainless steel A2 M1,6X2

Article number	51340.016.002
Brand	-
UBB	500633232862
UNSPSC	31161504
EAN	8715494592208
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1.6
Length	2 mm
Class	70
Driving features	Phillips
Head shape	Raised cheese head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M1.6
Thread length (min.)	15
dk (max.)	3.2
Full thread if $L \leq$	16
k	1.3
L (mm)	2
No. cross recess	0
P	0.35

Technical Drawing

