

Cross recessed raised cheese head screw Phillips DIN 7985-H Stainless steel A2 M1,6X10

Article number	51340.016.010
Brand	-
UBB	500633233282
UNSPSC	31161504
EAN	8715494592246
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1.6
Length	10 mm
Class	70
Driving features	Phillips
Head shape	Raised cheese head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M1.6
Thread length (min.)	15
dk (max.)	3.2
Full thread if $L \leq$	16
k	1.3
L (mm)	10
No. cross recess	0
P	0.35

Technical Drawing

