

Cross recessed raised cheese head screw Phillips DIN 7985-H Stainless steel A2 M3X4

Article number	51340.030.004
Brand	-
UBB	500633234504
UNSPSC	31161504
EAN	8715494592376
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	4 mm
Class	70
Driving features	Phillips
Head shape	Raised cheese head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	6
Full thread if $L \leq$	20
k	2.4
L (mm)	4
No. cross recess	1
P	0.5

Technical Drawing

