


Spring-type straight pin
slotted, light duty ISO
13337 Stainless spring steel
5X8MM



Article number	51431.050.008
Brand	-
UBB	500697297421
UNSPSC	31163201
EAN	8715492077950
PKG. of 500	Full Box Only

Technical Parameters

Length	8 mm
Material	Stainless spring steel
Info	Dimensions d1 and d2 in above table are before mounting.For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer.The type of austenitic stainless spring steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506.V = minimum shear strength, double, in kN (valid for steel pins only).The recommended tolerance class for the accommodating hole diameter d (nominal) is H12.Special features

Standards

ISO	13337
DIN	7346

of slotted spring-type straight pins: These pins are used to connect two or more construction elements to each other. They are highly suitable to absorb shear forces.

Technical Specification

a	0.5
a (min.)	0.5
d1 (max.)	5.6
d1 (min.)	5.4
d2 ≈	4.4
L (mm)	8
s	0.5
V	10.4

Technical Drawing

