



Taper pin, turned DIN 1 B
Stainless steel A1 2,5X24MM

Article number	51560.025.024
Brand	-
UBB	950359180516
UNSPSC	31163205
EAN	8715492295163
PKG. of 100	Full Box Only

Technical Parameters

Diameter	2.5 mm
Length	24 mm
Material	Stainless steel
Material technical	A1

Standards

ISO	≈2339-B
DIN	1-B

Info	<p>Taper pins are designed for the friction type fastening and/or locking together of two or more individual elements. The tapered shape allows the connection to be disconnected repeatedly, and when the elements are joined together again, their location remains as accurate as it was previously, and the frictional connection remains as strong as before. The nominal length (L, tolerance class js15) does not include the rounded ends. For taper pins with d1 = 20 distance W is at the choice of the user.</p>
------	---

Technical Specification

c (max.)	0.4
d1	2.5
d2	8
d2 ≤	9
D (mm)	2.5
L (mm)	24
r ≈	2.5
W (min.)	5

Technical Drawing

