


Cylindrical head srew with
cutting-point 5,0X100



Article number	51562.050.100
Brand	-
UBB	500634314362
UNSPSC	31161605
EAN	8715494625210
PKG. of 100	Full Box Only

Technical Parameters

Diameter	5 mm
Length	100 mm

Standards

Technical Specification

d2	6.4
D (mm)	5
dk	8.75
k	5.45
L (mm)	100
Socket	25

Technical Drawing

