



Grooved pin, full length taper grooved DIN 1471 Stainless steel A1 2X20MM

Article number	51585.020.020
Brand	-
UBB	500634427552
UNSPSC	31163215
EAN	8717077008762
PKG. of 500	Full Box Only

Technical Parameters

Diameter	2 mm
Length	20 mm
Material	Stainless steel
Material technical	A1

Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.
------	---

Standards

ISO	≈8744
NEN	≈2602
DIN	1471

Technical Specification

c ≈	0.25
d1	2
d2 ≈	2.15
D (mm)	2

Technical Drawing

L (mm)	20
r	2
Tolerance	h9
V	2.85

FABORY

