

## Grooved pin, full length taper grooved DIN 1471 Stainless steel A1 3X20MM



Article number	51585.030.020
Brand	-
UBB	500634428212
UNSPSC	31163215
EAN	8717077008830
PKG. of 500	Full Box Only

### Technical Parameters

Length (L) (mm)	20
d <sub>1</sub>	3
Diameter (mm)	3
Material	Stainless steel
Material technical	A1

**Info**

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d<sub>2</sub> is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d# (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

### Standards

DIN	1471
ISO	8744

### Technical Specification

c ≈	0.4
d <sub>2</sub> ≈	3.25
r ≈	3

### Technical Drawing

Tolerance	h9
V	6.15

