

## Grooved pin, full length taper grooved DIN 1471 Stainless steel A1 4X12MM



Article number	51585.040.012
Brand	-
UBB	500634428543
UNSPSC	31163215
EAN	8717077008861
PKG. of 200	Full Box Only

### Technical Parameters

Length (L) (mm)	12
d <sub>1</sub>	4
Diameter (mm)	4
Material	Stainless steel
Material technical	A1

**Info**

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d<sub>2</sub> is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d<sub>#</sub> (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

### Standards

ISO	8744
DIN	1471

### Technical Specification

c ≈	0.5
d <sub>2</sub> ≈	4.25
r ≈	4

### Technical Drawing

Tolerance h11  
V 10.6

