



Grooved pin, half length taper grooved DIN 1472 Stainless steel A1 2X12MM

Article number	51586.020.012
Brand	-
UBB	500634431265
UNSPSC	31163215
EAN	8717077009134
PKG. of 500	Full Box Only

Technical Parameters

Diameter	2 mm
Length	12 mm
Material	Stainless steel
Material technical	A1

Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.
------	---

Standards

DIN	1472
ISO	≈8745
NEN	≈2603

Technical Specification

c ≈	0.25
d1	2
d2 ≈	2.15
D (mm)	2

Technical Drawing

L (mm)	12
r	2
Tolerance	h9
V	2.85

FABORY

