



Grooved pin, one-third length center grooved DIN 1475 Stainless steel A1 3X6MM

Article number	51587.030.006
Brand	-
UBB	500697301538
UNSPSC	31163215
EAN	8715492080622
PKG. of 500	Full Box Only

Technical Parameters

Length	6 mm
Material	Stainless steel
Material technical	A1
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

ISO	≈8742
NEN	≈2606
DIN	1475

Technical Specification

c ≈	0.4
d1	3
d2 ≈	3.25
L (mm)	6

Technical Drawing

$r \approx$	3
Tolerance	h9
V	6.15

