



Grooved pin, one-third length center grooved DIN 1475 Stainless steel A1 3X14MM

Article number	51587.030.014
Brand	-
UBB	500697301793
UNSPSC	31163215
EAN	8715492080646
PKG. of 500	Full Box Only

Technical Parameters

Length	14 mm
Material	Stainless steel
Material technical	A1
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

DIN	1475
NEN	≈2606
ISO	≈8742

Technical Specification

c ≈	0.4
d1	3
d2 ≈	3.25
L (mm)	14

Technical Drawing

$r \approx$	3
Tolerance	h9
V	6.15

