



Cross recessed countersunk head tapping screw Phillips DIN 7982 C-H Stainless steel A2 ST2,2X25MM

Article number	51680.022.025
Brand	-
UBB	500571537231
UNSPSC	31161507
EAN	8715494123242
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	2.2 mm
Length	25 mm
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

DIN	7982 CH
NF	E25-656
ISO	7050 CH

Technical Specification

D (mm)	2.2
dk	4.3
k ≈	1.3
L (mm)	25
No. cross recess	1
P	0.8

Technical Drawing

