



Cross recessed countersunk head tapping screw Phillips DIN 7982 C-H Stainless steel A2 ST3,5X6,5MM

Article number	51680.035.006
Brand	-
UBB	500571345171
UNSPSC	31161507
EAN	8715494111171
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	6.5 mm
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

NF	E25-656
ISO	7050 CH
DIN	7982 CH

Technical Specification

D (mm)	3.5
dk	6.8
k ≈	2.1
L (mm)	6.5
No. cross recess	2
P	1.3

Technical Drawing

