



Cross recessed countersunk head tapping screw Pozidriv DIN 7982 C-Z Stainless steel A2 ST4,2X25MM

Article number	51681.042.025
Brand	-
UBB	950352778704
UNSPSC	31161507
EAN	8715492304759
PKG. of 200	Full Box Only

Technical Parameters

Diameter	4.2 mm
Length	25 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

ISO	7050 CZ
NF	E25-656 C
DIN	7982 CZ

Technical Specification

D (mm)	4.2
dk	8.1
k ≈	2.5
L (mm)	25
No. cross recess	2
P	1.4

Technical Drawing

