



Cross recessed raised countersunk head tapping screw Phillips DIN 7983 C-H Stainless steel A2 ST3,5X16MM

Article number	51690.035.016
Brand	-
UBB	950352200865
UNSPSC	31161507
EAN	8715492305596
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	16 mm
Driving features	Phillips
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

DIN	7983 CH
ISO	7051 CH
NF	E25-657

Technical Specification

D (mm)	3.5
dk	6.8
f ≈	1.2
k ≈	2.1
L (mm)	16
No. cross recess	2
P	1.3

Technical Drawing

