



Cross recessed raised countersunk head tapping screw Phillips DIN 7983 C-H Stainless steel A2 ST4,8X50MM

Article number	51690.048.050
Brand	-
UBB	950352204172
UNSPSC	31161507
EAN	8715492305930
PKG. of 200	Full Box Only

Technical Parameters

Diameter	4.8 mm
Length	50 mm
Driving features	Phillips
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

ISO	7051 CH
NF	E25-657
DIN	7983 CH

Technical Specification

D (mm)	4.8
dk	9.5
f ≈	1.5
k ≈	3
L (mm)	50
No. cross recess	2
P	1.6

Technical Drawing

