

Cross recessed raised countersunk head tapping screw Phillips DIN 7983 C-H Stainless steel A2 ST5,5X25MM



Article number	51690.055.025
Brand	-
UBB	950352204669
UNSPSC	31161507
EAN	8715492306029
PKG. of 200	Full Box Only

Technical Parameters

Diameter (mm)	5.5
Length (L) (mm)	25
Driving features	Phillips
Head shape	Raised countersunk head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread

Standards

NF	E25-657
DIN	7983 C-H
ISO	7051 C-H

Technical Specification

d_k	10.8
$f \approx$	1.7
$k \approx$	3.4
No. cross recess	3
P	1.80

Technical Drawing

