



Split pin (cotter pin) DIN 94 Stainless steel A2 1,6X14MM

Article number	51700.016.014
Brand	-
UBB	500633286249
UNSPSC	31163204
EAN	8715494597548
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	1.6 mm
Length	14 mm
Material	Stainless steel
Material technical	A2

Standards

ISO	1234
NEN	182
DIN	94
NF	E25-774

Info	Other types of stainless steel than specified (but with equal properties) may be supplied at the discretion of the manufacturer. The shape of the split pin ends are at the manufacturer's discretion. For stainless steel split pins the type of austenitic stainless steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506. The recommended tolerance class for the accommodating hole diameter d (nominal) is H13 for $d \leq 1,2$ mm and H14 for bigger diameters. The tolerance class of
------	--

the nominal length
(L) is js17.

FABORY

Technical Specification

a (max.)	2.5
b ≈	3.2
c (max.)	2.8
c (min.)	2.4
d (min.)	1.3
D (mm)	1.6
L (mm)	14
d (max.)	1.4

Technical Drawing

