



## Prevailing torque type hexagon nut with non- metallic insert, Metalform DIN 985 Stainless steel A2 METALFORM M10

Article number	51729.100.001
Brand	-
UBB	950355976818
UNSPSC	31161727
EAN	8715492307521
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	M10
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Surface treatment	METALFORM
Thread	Metric thread

#### Info

Specific features of Metalform: The fixed, slightly visible dry film lubricant reduces the effect of galling. It levels out the big scatter in coefficient of friction and reduces the average value. In a bolt/nut assembly only one product (e.g. the nut) needs to be lubricated with Metalform. The lubricant can easily be removed with a solvent after assembly, there's no objection against

### Standards

DIN	985
NF	E25-412
ISO	≈10511

application in the  
food industry.

# FABORY

## Technical Specification

d-D	M10
h	10
P	1.5
s	17

## Technical Drawing

