



**Prevailing torque type
hexagon nut with non-
metallic insert, Metalform
DIN 985 Stainless steel A2
METALFORM M20**

Article number	51729.200.001
Brand	-
UBB	950355977154
UNSPSC	31161727
EAN	8715492307552
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Surface treatment	METALFORM
Thread	Metric thread

Info

Specific features of Metalform: The fixed, slightly visible dry film lubricant reduces the effect of galling. It levels out the big scatter in coefficient of friction and reduces the average value. In a bolt/nut assembly only one product (e.g. the nut) needs to be lubricated with Metalform. The lubricant can easily be removed with a solvent after assembly, there's no objection against

Standards

NF	E25-412
ISO	≈10511
DIN	985

FABORY application in the
food industry.

Technical Specification

d-D	M20
h	20
P	2.5
s	30

Technical Drawing

