

Eye bolt DIN 444 B Stainless steel A2 50 M10X40



Article number	51790.100.040
Brand	-
UBB	951351855774
UNSPSC	31161610
EAN	8715492309693
PKG. of 10	Full Box Only

Technical Parameters

Length (L) (mm)	40
d ₁	M10
Diameter (d-D)	M10
Class	50
Material	Stainless steel
Thread direction	Right
Thread	Metric thread
Material technical	A2

Standards

DIN	444 B
-----	-------

Technical Specification

b (min.): 125mm < L ≤ 200mm	32
b (min.): L ≤ 125mm	26
d ₂ (H9)	10
d ₃ (max.)	20
P	1.50
s (max.)	12

Technical Drawing

