

Hexagon head screw DIN 933 Stainless steel A2 (AD-W2) 70 for pressure vessels M8X100

Article number	52011.080.100
Brand	-
UBB	500697424306
UNSPSC	31161620
EAN	8715492086754
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	100 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2 (AD-W2)
Thread	Metric thread

Info	Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W2, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a certificate EN 10204
------	--

Standards

ISO	4017
ASME	B18.2.3.1M
NF	E25-114
DIN	933
NEN	1568

3.1 by marking the fasteners with the property class and the manufacturer's mark. This recognition is equally accepted by Lloyd's Register Energy. Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50. for pressure vessels

Technical Specification

d-D	M8
k	5.3
L (mm)	100
P	1.25
s	13

Technical Drawing

