

## Hexalobular countersunk head screw DIN ≈965 A Stainless steel A4 80 M3X12



|                |               |
|----------------|---------------|
| Article number | 53345.030.012 |
| Brand          | -             |
| UBB            | 500690308779  |
| UNSPSC         | 31161504      |
| EAN            | 8717077788886 |
| PKG. of 1000   | Full Box Only |

### Technical Parameters

|                    |                  |
|--------------------|------------------|
| Diameter (d-D)     | M3               |
| Length (L) (mm)    | 12               |
| Class              | 80               |
| Driving features   | Hexalobular      |
| Head shape         | Countersunk head |
| Material           | Stainless steel  |
| Material technical | A4               |
| Thread direction   | Right            |
| Thread             | Metric thread    |

### Standards

|     |            |
|-----|------------|
| DIN | ≈965 A     |
| NF  | ≈E25-119-1 |
| ISO | ≈14581     |

### Technical Specification

|                         |      |
|-------------------------|------|
| Thread length (min.)    | 19   |
| $d_k$ (max.)            | 5.6  |
| Full thread if $L \leq$ | 22   |
| $k$ (max.)              | 1.65 |
| P                       | 0.50 |
| Socket                  | T10  |

### Technical Drawing

