

## Hexagon head bolt DIN 931 Stainless steel A4 80 M10X75

Article number	53510.100.075
Brand	-
UBB	500633303986
UNSPSC	31161620
EAN	8715494599320
PKG. of 50	Full Box Only

### Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	75
Class	80
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4
Wrench width (s) (mm)	17
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

### Standards

DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

### Technical Specification

b (min.): 125mm<L≤200mm	32
b (min.): L>200mm	45
b (min.): L≤125mm	26
k	6.4
P	1.50
s	17

### Technical Drawing

