

Hexagon head bolt DIN 931 Stainless steel A4 80 M14X75

Article number	53510.140.075
Brand	-
UBB	500633306799
UNSPSC	31161620
EAN	8715494599603
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M14
Length	75 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
NEN	1555
NF	E25-112
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	75
P	2
s	22

Technical Drawing

