

Hexagon head bolt DIN 931 Stainless steel A4 80 M14X95

Article number	53510.140.095
Brand	-
UBB	500633307037
UNSPSC	31161620
EAN	8715494599634
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M14
Length (L) (mm)	95
Class	80
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4
Wrench width (s) (mm)	22
Info	Sizes with a diameter M24 are minimal property class 50.

Standards

DIN	931
ASME	B18.2.3.1M
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mm<L≤200mm	40
b (min.): L>200mm	53
b (min.): L≤125mm	34
k	8.8
P	2
s	22

Technical Drawing

