

Hexagon head bolt DIN 931 Stainless steel A4 80 M14X120

Article number	53510.140.120
Brand	-
UBB	500633307375
UNSPSC	31161620
EAN	8715494599665
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M14
Length	120 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
ISO	4014
NF	E25-112
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	120
P	2
s	22

Technical Drawing

