

Hexagon head bolt DIN 931 Stainless steel A4 80 M16X250

Article number	53510.160.250
Brand	-
UBB	500633308852
UNSPSC	31161620
EAN	8715494599818
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M16
Length	250 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	250
P	2
s	24

Technical Drawing

