

Hexagon head bolt DIN 931 Stainless steel A4 80 M20X180

Article number	53510.200.180
Brand	-
UBB	500633309504
UNSPSC	31161620
EAN	8715494599887
PKG. of 10	Full Box Only

Technical Parameters

Diameter (d-D)	M20
Length (L) (mm)	180
Class	80
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A4

Info
 Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
DIN	931
NF	E25-112
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm<L≤200mm	52
b (min.): L>200mm	65
b (min.): L≤125mm	46
k	12.5
P	2.50
s	30

Technical Drawing

