

Hexagon head bolt DIN 931 Stainless steel A4 80 M24X70

Article number	53510.240.070
Brand	-
UBB	500633310247
UNSPSC	31161620
EAN	8715494599955
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	70 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NEN	1555
ASME	B18.2.3.1M
ISO	4014
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	70
P	3
s	36

Technical Drawing

