

Hexagon head bolt DIN 931 Stainless steel A4 80 M24X230

Article number	53510.240.230
Brand	-
UBB	500633310817
UNSPSC	31161620
EAN	8715494600019
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M24
Length	230 mm
Class	80
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	230
P	3
s	36

Technical Drawing

